



Food & Beverage

Fluke can help you save time, manage processes and increase productivity

Today's food and beverage manufacturers operate in a pressure cooker. Keeping the lid on production costs and energy expenditures can be a daily challenge. Regulatory requirements, safety issues, and the demands of maintaining uptime add another layer of complexity. Fluke has solutions to minimize waste, optimize equipment, prevent downtime and reduce energy consumption. Fluke tools are the industry standard against which other tools are measured.

Save more in 2024

For a limited time, you can take advantage of significant price discounts on a wide range of Fluke tools and care plans. Whether you are a professional electrician, facility maintenance engineer, Food & Beverage manager, or a Distributed Energy technician, this promotion offers you the opportunity to upgrade your toolbelt with top-quality Fluke solutions at fantastic prices.



Fluke 87V/E2 Industrial Electrician Combo Kit

Fluke 87V

The Fluke 87V TRMS Multimeter provides the resolution and accuracy to efficiently troubleshoot motor drives, plant automation, power distribution, and electromechanical equipment even in loud, high energy, and high altitude locations.

Item No.: 1895811
Code: FLUKE 87-5/E2K/EUR

Save 11%

C35 Soft Carrying Case

Holds meter, test leads and other accessories.

Fluke TPAK ToolPak™ Magnetic Meter Hanger

It allows you to hang your meter on nails, hooks, and pipes so you can take hands-free measurements.



Fluke 279FC/iFlex True-RMS Thermal Multimeter with iFlex

A full-featured multimeter with built-in thermal imager that reveals hot spots that may indicate electrical issues quickly and safely.

Item No.: 2542638
Code: FLUKE-279FC/IFLEX

Save 13%

Delivered with iFlex® (a flexible current clamp) to expand your measurement capabilities and get into tight, hard to reach spaces for current measurement (up to 2500 A AC).



Fluke 378FC Non-Contact Voltage True-RMS AC/DC Clamp Meter with iFlex

It uses FieldSense™ technology to make testing faster and safer, all without contacting a live conductor.

You get accurate voltage and current measurements through the clamp jaw.

Delivered with iFlex® (a flexible current clamp) to expand your measurement capabilities and get into tight, hard to reach spaces for current measurement (up to 2500 A AC).

Item No.: 3744634
Code: Fluke 378FC

Save 11%





Fluke 568 Infrared and Contact Thermometer

With a 50:1 distance-to-spot ratio, you can measure smaller objects from further away. And the rugged, ergonomic design is built to withstand tough industrial, electrical, HVAC, and mechanical environments.

Item No.: 1503752
Code: Fluke 568

Save 23%



Fluke 1738 Three-Phase Power Quality Logger

Built with Fluke Connect® mobile app and desktop software compatibility gives you the data you need to make critical power quality and energy decisions in real-time. Now you can perform advanced analysis with an enhanced Power Quality Health Summary (EN50160) function that provides you with fast insight into overall electrical system health.

Item No.: 2499714
Code: Fluke 1738

Save 7%

Item No.: 4544258
(with Premium Care)
Code: Fluke 1738/FPC EU

Premium Care

Reduce unplanned expenses and get the most out of your tools.

Coverage that prevents unexpected downtime caused by damaged test equipment, accessories, or tools in need of calibration or repair.

Save 11%



Fluke 773 Milliamp Process Clamp Meter

Save time and money by measuring 4–20 mA signals five times faster than with traditional multimeters, and without breaking the loop. That means you can troubleshoot a live device without having to power down and possibly miss something going on in the process.

Item No.: 2422947
Code: 773

Save 10%



Fluke 1587FC Insulation Multimeter

Fluke Connect + Fluke's 1587 FC Insulation Multimeter helps you identify tough problems, fix, and wirelessly communicate your work quickly and easily - all at a safe distance.

Item No.: 2507342
Code: 1587FC

Save 8%



Fluke MDA-550 Series III Motor Drive Analyzer

MDA-550 Series III Motor Drive Analyzer Simplify complex motor-drive troubleshooting with guided test setups and automated drive measurements that provide reliable, repeatable test results.

Item No.: 4566116
Code: Fluke MDA-550-III

Save 5%

Premium Care

Reduce unplanned expenses and get the most out of your tools.

Coverage that prevents unexpected downtime caused by damaged test equipment, accessories, or tools in need of calibration or repair.

Item No.: 4566118
(with Premium Care)
Code: Fluke MDA-550/FPC

Save 12%



Save up to 20% on selected Fluke products



Savings are calculated by taking the list prices of the items separately. Promotion valid until 31.12.2024. ©2024 Fluke Corporation. Information subject to change without prior notice. 10/2024 240534-uken

Exclusive bundles 2024

Explore the various exclusive bundles at Farnell, carefully selected to deliver performance and provide you with cost savings.

FLUKE 289/FVF/EUR

16% off



A high-performance multimeter designed for industrial and electronics professionals bundled with the FlukeView software.

- **Predictive maintenance:** logging data over time and analyzing trends, users can detect potential equipment issues before they lead to costly downtime.
- **Maximized Productivity:** enables efficient troubleshooting, accurate measurements, and comprehensive data documentation.

Item number: 1895817

FLUKE 179/EDA2/EUR

16% off



The kit includes the Fluke 179 True-RMS Digital Multimeter, TL224 SureGrip Silicone Test Lead Set, and AC280 SureGrip Hook Clips for comprehensive, accurate, and safe electrical measurements.

- **Accurate measurements:** the multimeter with its True-RMS capabilities ensures accurate measurements of AC voltage and current, essential for troubleshooting electrical systems.
- **Hands-Free Testing:** the SureGrip Hook Clips allow technicians to perform hands-free testing, improving safety and efficiency when working with live circuits or tight spaces.

Item number: 1895812

51% off

FLUKE 115/TLK225-1



The combination of the Fluke 115 True-RMS Digital Multimeter with the TLK225-1 SureGrip™ Master Accessory Set, provides a comprehensive solution for electrical troubleshooting with versatile measurement capabilities and a range of essential accessories.

- **Efficient electrical troubleshooting:** identify and diagnose electrical issues such as voltage fluctuations, continuity problems, and faulty components.
- **Versatile Measurement Needs:** whether it's testing AC voltage and current, resistance, continuity, diodes, or using various accessories for specific measurements, making it suitable for diverse troubleshooting scenarios.

Item number: 2523073

12% off

FLK-87V-EUR/PRV240



The kit combines the Fluke 87V True-RMS Digital Multimeter with the Fluke PRV240 Proving Unit, offering robust industrial troubleshooting capabilities and safe voltage detector testing in one package.

- **Safety in Voltage Testing:** The Fluke PRV240 Proving Unit ensures safe voltage testing by verifying the functionality of voltage detectors before live testing, preventing accidents, and ensuring precision in hazardous environments.
- **Reliable Voltage Testing:** The Fluke PRV240 Proving Unit ensures accurate voltage testing, reducing errors and improving efficiency in electrical troubleshooting.

Item number: 4399582

Capture more than you expect.

FLUKE®



Buy one of the selected cameras

and get a free Fluke product!



Limited time offer: September 1st - December 15th, 2024

Now is the time to buy that Fluke thermal camera you've been eyeing. But which thermal imager will you choose?

Purchase One



Fluke Ti300+ Thermal Camera

- Focused images with LaserSharp™ Auto Focus
- 2-meter drop test
- Measure up to 650°C



Fluke Ti401 Pro Thermal Camera

- Increased flexibility to capture measurements
- Unique combination of 640x480 resolution
- Patented IR-Fusion™ technology



Fluke Ti480 PRO Thermal Camera

- Increased sensitivity
- Sharper onscreen images
- Interchangeable smart lenses
- Wireless connectivity and reporting



Fluke TiX501 Thermal Camera

- Interchangeable Smart Lenses
- Edit and analyze images on camera
- Large 5.7 inch LCD touchscreen technology



Fluke TiX580 Thermal Camera

- Unmatched shooting flexibility (180-degree articulating lens)
- On-board advanced analytics
- Responsive LCD touchscreen
- On-camera boosted resolution

Choose One



Free Fluke 2X Telephoto Infrared Smart Lens



Free Fluke Wide angle Infrared Smart Lens



Free Fluke 279 FC True-rms Thermal Multimeter



Free Fluke PTi120 Pocket Thermal Camera

How to qualify for the promotion and redeem your free Fluke tool.

1. Buy one of the selected Fluke Thermal Imaging cameras between 1 September and 15 December 2024
 - Purchase must be made from an authorized Fluke distributor.
 - Proof of sale in form of a receipt or invoice is required.
(Packing slip, purchase orders/order confirmations are not acceptable as proof of purchase)
 - Qualified Fluke thermal imagers include: Fluke Ti300+, Ti401PRO, Ti480PRO, TiX501 and TiX580.
2. Claim your Free Fluke tool here: www.fluke.co.uk/freefluke
3. Receive and enjoy your new Free Fluke product!

Learn more about this promotion and the qualified Fluke Thermal Imaging cameras.

Visit www.fluke.co.uk/freefluke

©2024 Fluke Corporation. 220796-en